


Deck 1



Deck 1 has dedicated end posts for each run, and the posts are situated such that the back side of the posts are all accessible, meaning you can use an *outside-of-post to outside-of-post* configuration for all runs. This is both the most economical solution and where the fittings are least visible.

Options for all runs on Deck 1:

If wood posts, use the 262 series.

The tensioning device is a 3½"-long Invisiware® Receiver, which installs flush through the wood post on one end. A Pull-Lock fitting is installed through the other end.

If 2" metal posts, use the 232 series; if 1½", use the 212 series.

The tensioning device is a 2" - (or 1½"-) long Invisiware Receiver, which installs flush through the metal post on one end. A Pull-Lock fitting is installed through the other end.



Railing Kits for Deck 1

Cable Length	1/8" cable			3/16" cable		
	wood post PART NO.	2" metal post PART NO.	1½" metal post PART NO.	wood post PART NO.	2" metal post PART NO.	1½" metal post PART NO.
5'	26205	23205	21205	26205-6	23205-6	21205-6
10'	26210	23210	21210	26210-6	23210-6	21210-6
15'	26215	23215	21215	26215-6	23215-6	21215-6
20'	26220	23220	21220	26220-6	23220-6	21220-6
25'	26225	23225	21225	26225-6	23225-6	21225-6